

RadFlash® Electronic Personal Dosimeter is a miniature dosimeter capable of solving a wide range of personal dose monitoring tasks, including measurement of personal dose equivalent and personal dose equivalent rate of X-ray (continuous and pulsed) and gamma radiation.

When used with PM530 dosimetry software, RadFlash provides assurance that occupational radiation exposures are accurately measured, analyzed, and reported. RadFlash allows for avoiding overexposure by providing **real-time** measurements and timely warning the wearer that the dose and dose rate thresholds are exceeded. This ensures that specialists can respond quickly and minimize potential health risks.

RadFlash is compatible with the free Polismart® App that delivers radiation exposure analytics and insights to users and enables wireless transfer, analysis, and reporting of the exposure data captured by the dosimeter. Polismart allows for tracking exposure and adjusting dosimeter settings anytime, anywhere, solely with your smartphone.

Applications

- Healthcare workers
 - Interventional radiology
 - Medical physicists
 - Radioisotope labs
 - X-ray diagnostics
- Customs and border control officers working with X-ray inspection equipment
- Anyone working under the risk of X–ray and gamma radiation exposure

Features

- Simple dose reads via smartphone or PC at any time
- Easy setup via free Polismart® iOS and Android app
- Clips and a wristband for different wearing options
- Resistance to cleaning and disinfection agents
- On-screen, audible and visual (LED) alarms
- Data transfer via Bluetooth
- Small and lightweight
- Single control button
- Wireless charging



RadFlash ELECTRONIC PERSONAL DOSIMETER



SPECIFICATIONS	
Detector	Geiger-Mueller tube
Dose rate measurement range	0.1 μSv/h to 1 Sv/h
Dose rate measurement accuracy	±15 %
Dose measurement range	1 μSv to 10 Sv
Dose measurement accuracy	±15 %
Energy range	15 keV to 1.5 MeV
Energy response relative to 0.662 MeV (137Cs)	-29 % to +45 %
Minimum pulse duration of pulsed X-ray radiation	2 ms

Memory	6000 events	
Alarms	visual, audible	
Communication	Bluetooth 4.0 (FCC ID: QOQ13, IC: 5123A-13)	
Power supply	rechargeable battery (wireless charger provided)	
Rattery lifetime	<u> </u>	

Battery lifetime

– Bluetooth off, dose rate < 0.3 μSv/h ≥ 2 months – Bluetooth on, dose rate < 0.3 μ Sv/h ≥ 10 days Bluetooth on, dose rate < 1 Sv/h ≥ 8 hours

Ingress protection	IP67
Drop test	1.5 m
Dimensions	≤ 63 × 50 × 18 mm
Weight	≤ 50 g
Operating conditions	
 ambient temperature 	–10 °C to 50 °C
 atmospheric pressure 	84 kPa to 106.7 kPa



Compatible with **Real-Time Dosimetry Systems**



Compatible with free Polismart iOS and Android App



up to 98 % at 35 °C

Compatible with PM530 Automated Personal Dosimetry System







relative humidity



Three clips and a silicone wrist band for multiple wearing options

Polimaster Inc.

44873 Falcon Place, Suite 128 Sterling, VA 20166, USA phone: +1 703 525 5075 fax: +1 703 525 5079 info@polimaster.us

Polimaster Europe UAB

Ezero str. 4, Didziasalio k., Nemezio sen., LT-13264, Vilnius district, Lithuania phone: +370 5 210 2323 +370 5 210 2324 info@polimaster.com

Polimaster Japan Co., Ltd.

AUBE2 5-177 Kuratsuki, Kanazawa, Ishikawa Prefecture 920-8203 Japan phone: + 81 076 201 8623 fax: + 81 076 201 8624 pacific@polimaster.jp